

Description	Capacity	Maximum RCF	Maximum Speed	Supplier No.
45° Fixed Angle Rotor, Model F2402H	24 x 1.5–2.0 mL	61,970 <i>g</i> (Allegra 64R), 19,280 <i>g</i> (Allegra X-30), 28,672 <i>g</i> (Allegra X-30R)	26,000 rpm (Allegra 64R), 14,500 rpm (Allegra X-30), 18,000 rpm (Allegra X-30R)	361171
25° Fixed Angle Rotor, Model F1010	10 x 10 mL	57,440 <i>g</i> (Allegra 64R), 17,896 <i>g</i> (Allegra X-30), 27,579 <i>g</i> (Allegra X-30R)	26,000 rpm (Allegra 64R), 14,500 rpm (Allegra X-30), 18,000 rpm (Allegra X-30R)	361221
30° Fixed Angle Rotor, Model F0630	6 x 30 mL	59,860 <i>g</i> (Allegra 64R), 18,367 <i>g</i> (Allegra X-30), 28,305 <i>g</i> (Allegra X-30R)	26,200 rpm (Allegra 64R), 14,500 (Allegra X-30), 18,000 rpm (Allegra X-30R)	361231
Biosafe Bowl Rotor, Model H6002	60 x 1.5–1.8 mL, 72 x 600 µL, 84 x 250 µL	12,400 <i>g</i>	12,200 rpm	363000
45° Fixed Angle Rotor, Model F3602	36 x 1.5–2.0 mL	46,530/41,660 <i>g</i>	22,000 rpm	364600
25° Fixed Angle Rotor, Model F0650	6 x 50 mL	41,400 <i>g</i>	21,000 rpm	364610
30° Fixed Angle Rotor, Model F0485	4 x 85 mL	40,240 <i>g</i>	20,000 rpm	364620
45° Fixed Angle Rotor, Model F1202	12 x 1.5–2.0 mL	64,400 <i>g</i>	30,000 rpm	364630
25° Fixed Angle Rotor, Model F0850	8 x 50 mL	29,220 <i>g</i> (Allegra 64R), 8528 <i>g</i> (Allegra X-30), 13,682 <i>g</i> (Allegra X-30R)	16,500 rpm (Allegra 64R), 9000 rpm (Allegra X-30), 11,400 rpm (Allegra X-30R)	364640
25° Fixed Angle Rotor, Model F0685	6 x 85 mL	26,320 <i>g</i> (Allegra 64R), 6953 <i>g</i> (Allegra X-30), 10,864 <i>g</i> (Allegra X-30R)	15,500 rpm (Allegra 64R), 8000 rpm (Allegra X-30), 10,000 rpm (Allegra X-30R)	364650
Swinging Bucket Rotor, Model S0410	4 x 10 mL	10,733 <i>g</i>	10,000 rpm	364660
25° Conical Fixed Angle Rotor, Model C0650	6 x 50 mL	10,400 <i>g</i> (Allegra 64R), 10,304 <i>g</i> (Allegra X-30R), 8346 <i>g</i> (Allegra X-30)	10,000 rpm (Allegra 64R and Allegra X-30), 8346 rpm (Allegra X-30R)	364670
25° Conical Fixed	10 x 15 mL	10,400 <i>g</i>	10,000 rpm (Allegra	364680

Angle Rotor, Model C1015	(Allegra 64R), 8437 <i>g</i> (Allegra X-30), 10,416 <i>g</i> (Allegra X- 30R)	64R and Allegra X- 30R), 9000 (Allegra X-30)	
-----------------------------	--	--	--