

# ABT-HC-AFS-1420



Images



# **Product Data Sheet**

14 CF General Purpose Auto Defrost Laboratory

# Product Description

Auto-Defrost Freezers are ideal for industrial, clinical, or research laboratory Auto-Detrost Freezers are used for industrial, clinical, or research aboratory requirements. Designed to provide dependable, energy-efficient performance, all units are manufactured with CFC-free high-density urethane foam cabinet and door insulation to maintain temperature stability.

Auto-Defrost design provides the convenience of a frost-free interior. However, chamber air temperatures do experience a moderate rise during defrost cycles. Environmentally friendly, natural hydrocarbon (HC) refrigerants (not containing hydrofluorocarbons) vastly reduce global-warming potential (GWP) while meeting new EPA/SNAP mandates and UL, ASHRAE compliance guidelines.

DISCLAIMER: Auto defrost freezers incorporate an electric heater installed on the evaporator that assist in the removal of the frost and ice. Although the heater helps speed up the frost and ice removal, it can raise the temperatures within the freezer.

#### Storage capacity (cu. ft) 14 Cu. Ft. One solid swing door, right hinged Door Shelves Four adjustable shelves 1 wire basket Mounting Leveling Legs Interior lighting N/A External probe access 3/4" probe HFC Free high density urethane foam Exterior materials White powder coated steel General warranty One (1) year parts and labor warranty Compressor Parts Warranty Five (5) year compressor parts warranty Warranty Disclaimer Product Weight (lbs) 180 Shipping Weight (Ibs) 220 Rated Amperage Power Plug/Power Cord 5 Amps NEMA 5-15 Plug Facility Electrical Requirement

Refrigeration System	
Refrigerant	R600a
Defrost	Auto Defrost

### Controller, Configuration, Alarms and Monitoring Controller technology Mechanical thermostat

Adjustable Temperature Range -15°C - -20°C External alarm connection

Disclaimers DISCLAIMER: Auto defrost freezers incorporate an electric heater installed on the evaporator that assist in the removal of the frost and ice. Although the

heater helps speed up the frost and ice removal, it can raise the temperatures within the freezer.

nensions					
	Width (in.) 28"	Depth (in.) 26.25"	Height (in.)	Door Swing (in.) 25.75"	Total open Depth (in.) 67.75"
Exterior			67.75"	25.75"	67.75"
Interior	21.375"	14.25"	59.75"		
	1				
	← 28" →				
		<b>†</b>		=0_	
		5	<b>†</b>   <b>†</b>	1	
	S.5" 12" Probe Hole	67.75"	59.75" 26.25"		
	Hole Hole	14.25" —	→   ' · · · · ·		
				52"	
				1	
	0		<u> </u>	<u></u> М	
	21.375"				
		)			
				·	
		<b>+</b>		<u> </u>	
Service	800-648-4041 Option 3			customerservice@horizonscientific.com	1

800-648-4041 Option 5, Parts Option 4 Technical Service technicalservice@horizonscientific.com