

byko-visc DS

Stormer Type Viscometer

The byko-visc DS has a direct digital readout of Krebs units (KU), centipoise (cP), and grams (gm). The instrument rapidly calculates viscosity values. The digital stormer maintains the rotational speed at 200 rpms in compliance with ASTM D 562. The viscometer automatically starts and stops the motor shaft rotation by lowering or raising the instrument stand.

- Easy to use – automatic rotational speed control
- Automatically calculates KU, centipose, and gram units
- Printer interface for test report output
- Instrument base accessory to fit quart, pint, 1/2 pint containers
- Calibrated with NIST traceable oils
- Universal power supply – One model for global use

Standards

ASTM	D 562
------	-------



Ordering Information

Cat. No.	Description
8324	byko-visc DS

Comes complete with:

Viscometer,
1 paddle spindle,
Adapter for 1 pint,
1/2 pint containers,
Operation Manual

Technical Specifications

Range	Resolution	Accuracy	Repeatability	Spindle Speed
40-141 KU;	0.1 KU	within $\pm 1\%$	within $\pm 0.5\%$	200 rpm
32-1090 grams;	1.0 gm	full scale	full scale	± 0.1 rpm
27-5274 cP*	0.7 cP			
Voltage		100 - 230V/ 50-60Hz		
Operating Temperature		10 - 40 °C (50 - 104 °F)		
Dimensions		20 x 11 x 15 in		
Shipping Weight		10 kg (20 lbs)		

***Note:** Centipoise values are based on the conversion from Krebs Units as defined in the ASTM standard D562