


Benchmark 


# INCUSHAKE<sup>®</sup> Series

## Shaking Incubators

- + **Exceptional temperature uniformity**
- + **Miniature and cooling options available**
- + **Exchange flask clamps in one second with the new **MAGiC CLAMP™** magnetic system**



INCUSHAKE<sup>®</sup> Mini




INCUSHAKE<sup>®</sup> 10L

WITH  
**MAGiC CLAMP**  
PATENT PENDING






Incu-Shaker 10L (H2010)



Incu-Shaker Mini (H1001-M)



Technical Data:

|                           |                                           |
|---------------------------|-------------------------------------------|
| Temperature Range (Mini): | Ambient +5 to 70°C (Increments of 0.1°C)  |
| Temperature Range (10L):  | Ambient +5 to 60°C (Increments of 0.1°C)  |
| Temperature Range (10LR): | Ambient -15 to 60°C (Increments of 0.1°C) |
| Temperature Uniformity:   | +/- 0.25 %                                |
| Temperature Accuracy:     | +/- 0.1 %                                 |
| Shaking Speed Range:      | 30 to 300rpm (Increments of 1rpm)         |
| Shaking Orbit:            | 19mm (3/4")                               |
| Platform Dimensions:      |                                           |
| Incu-Shaker Mini          | 9.5 x 11.5 in. / 23.5 x 29.2 cm           |
| Incu-Shaker 10L/LR        | 17.8 x 17.8 / 45 x 45 cm                  |
| Exterior Dimensions:      |                                           |
| Incu-Shaker Mini          | 11 x 18.8 x 13 in. / 28 x 48 x 33 cm      |
| Incu-Shaker 10L           | 20 x 26 x 19 in. / 51 x 65 x 47 cm        |
| Incu-Shaker 10LR          | 20 x 31 x 22 in. / 51 X 79 X 56 cm.       |
| Weight:                   |                                           |
| Incu-Shaker Mini          | 25 lbs. / 11.5 kg                         |
| Incu-Shaker 10L           | 120 lbs / 55 kg                           |
| Incu-Shaker 10LR          | 170lbs / 78 kg                            |
| Electrical:               | 120 or 230V, 50-60Hz                      |

Ordering Information

|          |                                                               |
|----------|---------------------------------------------------------------|
| H1001-M* | Incu-Shaker Mini, includes standard rubber mat platform, 115V |
| H2010*   | Incu-Shaker 10L, includes standard rubber mat platform, 115V  |
| H1012*   | Incu-Shaker 10LR, includes standard rubber mat platform, 115V |

\*To order an item in 230V, add (-E) to item number.

Optional Platforms and Shelves

|            |                                                                                                        |
|------------|--------------------------------------------------------------------------------------------------------|
| H1000-MR   | MAGic Clamp universal platform, for Incu-Shaker Mini (9.5x11.5")                                       |
| H1010-MR   | MAGic Clamp universal platform, for Incu-Shaker 10L/LR (18x18")                                        |
| H1000-P-MP | Microplate platform, 4 position for Incu-Shaker Mini                                                   |
| H1010-P-MP | Microplate platform, 6 position for Incu-Shaker 10L/LR                                                 |
| H1000-P-SP | Spring rack platform, holds uncommon vessels for Incu-Shaker Mini                                      |
| H1010-P-SP | Spring rack platform, holds uncommon vessels for Incu-Shaker 10L/LR                                    |
| H1010-SH   | Optional Shelf, for Petri Dishes, microplates, trays, etc. (14 x 5.5") for Incu-Shaker 10L/LR (max. 3) |

Flask & Tube Rack Accessories for MAGic Clamp Platforms

|               |                                                                                                              |
|---------------|--------------------------------------------------------------------------------------------------------------|
| H1000-MR-50   | Flask Clamp, 50ml (H1000-MR: max. 20 / H1010-MR: max. 49)                                                    |
| H1000-MR-125  | Flask Clamp, 125ml (H1000-MR: max. 12 / H1010-MR: max. 36)                                                   |
| H1000-MR-250  | Flask Clamp, 250ml (H1000-MR: max. 8 / H1010-MR: max. 25)                                                    |
| H1000-MR-500  | Flask Clamp, 500ml (H1000-MR: max. 5 / H1010-MR: max. 16)                                                    |
| H1000-MR-1000 | Flask Clamp, 1000ml (H1010-MR: max. 9)                                                                       |
| H1000-MR-2000 | Flask Clamp, 2000ml (H1010-MR: max. 5)                                                                       |
| H1000-MR-MP   | Microplate Clamp, (H1000-MR: max. 4 / H1010-MR: max. 6)                                                      |
| H1000-MR-1550 | Tube Rack, 20x50 & 30x15 ml tubes (H1000-MR: max.1 / H1010-MR: max. 4)                                       |
| H1000-MR-T15  | Tube Rack, 32x15 tubes (H1000-MR: max. 2 / H1010-MR: max. 8)                                                 |
| H1000-MR-T50  | Tube Rack, 15x50 tubes (H1000-MR: max. 2 / H1010-MR: max. 8)                                                 |
| H1000-MR-T600 | Bottle Rack, 4x500/600ml conical bottles (H1000-MR: max. 1 / H1010-MR: max. 2)                               |
| H1000-MR-T5R  | MAGic Clamp™ tilted holder for 15mL and 50mL tube racks                                                      |
| H1000-MR-CMB  | Adjustable flask clamp for MAGic clamp platform, accepts 125ml (max. 36), 250ml (max. 25) or 500ml (max. 16) |



See it on the web!

Maximum capacity of Erlenmeyer flasks

| Flask Size: | Incu-Shaker Mini | Incu-Shaker 10L/LR |
|-------------|------------------|--------------------|
| 50ml        | 20               | 49                 |
| 125ml       | 12               | 36                 |
| 250ml       | 8                | 25                 |
| 500ml       | 5                | 16                 |
| 1L          | 2                | 9                  |
| 2L          | 0                | 5                  |