

# Branson™ Sonifier Cell Disruptor

Acoustic Enclosure

## Overview

Operating the Sonifier® in the Soundproof Enclosure can minimize mechanical noise produced by ultrasonic processing. The sturdy cabinet is lined with waterproof, sound-absorbing material, which is impervious to most solutions or laboratory reagents and can be easily cleaned. A fully-transparent door enables viewing of the process while limiting the noise to an acceptable level.

The decibel rating will lower by 20-25db.

Openings at the top and bottom of enclosure make for easy access for use with either a cup horn or standard probes.

Comes with inside column and adjustable clamp plate.

Side panel allows for placement of horns, tips and manuals.



## Specifications

| Actual Weight | Shipping Weight | I.D.                                         | O.D.                                          | Part #      | Adapter #                                |
|---------------|-----------------|----------------------------------------------|-----------------------------------------------|-------------|------------------------------------------|
| 19.5 lbs.     | 30 lbs.         | 13"W x 11"D x 21.5"H<br>(330 x 280 x 5466mm) | 18.5"W x 12.5"D x 28"H<br>(470 x 318 x 711mm) | 101-063-275 | 100-121-074<br>(Only Needed for SFX 150) |

For more information:  
[www.Emerson.com/Branson](http://www.Emerson.com/Branson)

**BRANSON™**



Authorized Distributor: Labequip Ltd Suite 409 1-7357 Woodbine Ave Markham, ON L3R 6L3 [www.labequip.com](http://www.labequip.com)

Get it from your authorized distributor: [www.labequip.com](http://www.labequip.com)



[ask@labequip.com](mailto:ask@labequip.com)