byko-spectra basic

For general color evaluation under defined lighting conditions the byko-spectra basic light booth offers the following benefits:

- Comparison of standard and sample in a color-neutral environment
- Three different controlled light sources:

Daylight D65 Incandescent light A

Department store light CWF or TL84

- Easy to operate by using individual switches for each light source
- Can be set up in minutes without any tools
- Economical testing of large samples in a compact design for laboratory and production



Standards						
ASTM	D 1729					
ISO	3668 (accessory required)					

Ordering Information				
Cat. No.	Description			
CV-6054	byko-spectra <i>basic</i>			
CV-6052	byko-spectra <i>basic</i>			
CV-6051	byko-spectra <i>basic</i>			
CV-6053	byko-spectra <i>basic</i>			

Comes complete with:

byko-spectra *basic* light booth 3 light sources: D65, A, CWF or TL84

Operating instructions

tions				
D65	Α	CWF	TL84	
X	Х		Х	
X	Х	Х		
X	Х	Х		
X	Х		Х	
48 x 67 x 42 cm (19 x 26.5 x 16.5 in)				
37 x 60 x 33 cm (15 x 24 x 13 in)				
14kg (30 lbs)				
	X X X X 48 x 67 x 42 cm (1 37 x 60 x 33 cm (1	D65 A X X X X X X X X X X X X 48 x 67 x 42 cm (19 x 26.5 x 16. 37 x 60 x 33 cm (15 x 24 x 13 in	D65 A CWF X X X X X X X X X X X X 48 x 67 x 42 cm (19 x 26.5 x 16.5 in) 37 x 60 x 33 cm (15 x 24 x 13 in)	

Ordering Information		Accessories				
Cat. No.	Description	Voltage	D65	A	CWF	TL84
CV-6055	Replacement Lamp Kit CWF	230 / 115 V	X	X	Х	
CV-6056	Replacement Lamp Kit TL84	230 / 115 V	X	X		X
CV-6058	Insert Panel Set for ISO 3668					
	(Includes side walls, rear wall and floor panels)					

 $\textbf{Note:} \ \ \text{We recommend to replace the lamps every 2500 hours.}$



170 Shields Court Unit 2 Markham, ON L3R 9T5 <u>TEL</u>: (905) 475-5880 ext. 226 <u>FAX</u>: (905) 475-1231