

ORBI-SHAKER"

Orbital Shaker Series













- Four versatile models covering a full range of applications
- Powerful, brushless motor drive systems - Attach flask clamps in one second with unique MAGic Clamp™ platform



9.5 x 8 in.

	Technical Dat	echnical Data:	
1	Speed Range:	50 to 300 rpm	
	Speed Increment:	10 rpm	
	Orbit:	19mm (3/4 in.)	
	Maximum Capacity:	4 x 1L or 4 kg	
	Standard Platform Dims.	9.5x8 in. / 24x20 cm	
	Dimensions (WxDxH):	13.1x11.74x4.7 in.	
		33x30x12 cm	
Ì	Weight:	12 lbs. / 5.5 kg	
	Operating Temp.:	4 to 65 ℃	
	Electrical:	100 - 240V 50-60Hz	

ORBI-SHAKER™JR.

Perfectly circular 19mm orbit for aeration and mixing

- ightharpoonup Digital speed control up to 300 rpm
- Image: Available with MAGic Clamp™ Platform

2

Patent Pending

13 x 12 in.

The Orbi-Shaker JR. is a space-saving shaker, complete with a 9.5 x 8 in. non slip, rubber coated platform that is ideal for tissue culture flasks, petri dishes and staining trays.

Additional platforms are also available for the Orbi-Shaker JR, including the convenient MAGic Clamp™ platform (patent pending) for use with Erlenmeyer flasks and test tube racks. The unique, magnetic attachment method is the easiest way to instantly change between flask clamps of different sizes.

Ordering Information:

BT302*	Orbi-Shaker JR with non-slip, rubber mat platform (9.5 x 8 in.)
H1000-MR	MAGic Clamp™ universal platform (9.5x11.5") for flasks & tube racks
H1000-MR-50	Clamp for Magic Clamp platform, 50ml (max. 20)
H1000-MR-125	Clamp for Magic Clamp platform, 125ml (max. 12)
H1000-MR-250	Clamp for Magic Clamp platform, 250ml (max. 8)
H1000-MR-500	Clamp for Magic Clamp platform, 500ml (max. 6)
H1000-MR-1000	Clamp for Magic Clamp platform, 1000ml (max. 4)
H1000-MR-1550	Tube rack for Magic Clamp platform, 12x50 and 21x15 ml conical tubes (max.)
BT300-RP	Rolling bar platform for uncommon vessels

^{*}To order an item in 230V, add (-E) to item number.

ORBI-SHAKER™






 Available with the MAGic Clamp™ Platform

The powerful Orbi-Shaker is capable of mixing a 14lb load capacity up to speeds as high as 300 rpm. The standard platform (included) features a non-slip, rubber coated surface, ideal for tissue culture flasks, petri dishes and staining trays.

The convenient MAGic Clamp $^{\text{m}}$ platform (patent pending) is also available for use with Erlenmeyer flasks and test tube racks. The unique, magnetic attachment method is the easiest way to instantly change between flask clamps of different sizes.



Ordering Information:

BT3001*	Orbi-Shaker™ Orbital Shaker with non-slip rubber mat platform (13 x 12 in.
BT3000-MR	MAGic Clamp™ universal platform (14x12") for flasks & tube racks
H1000-MR-50	Clamp for MAGic Clamp platform, 50ml (max. 30)
H1000-MR-125	Clamp for MAGic Clamp platform, 125ml (max. 24)
H1000-MR-250	Clamp for MAGic Clamp platform, 250ml (max. 14)
H1000-MR-500	Clamp for MAGic Clamp platform, 500ml (max. 9)
H1000-MR-1000	Clamp for MAGic Clamp platform, 1000ml (max. 5)
H1000-MR-2000	Clamp for MAGic Clamp platform, 2000ml (max. 2)
H1000-MR-1550	Tube rack for MAGic Clamp platform, 12x50 and 21x15 ml conical tubes (max. 2)
H1000-P-MP	Dedicated platform, 4x microplates (standard or deepwell)
H1000-P-SP	Spring rack platform, for uncommon vessels and containers
	*To order an item in 230V, add (-E) to item number.



3mm orbit, optimized for thorough mixing in microplates Digital speed control up to 1500 rpm

Holds up to four microplates

This vortexer is designed with a 3mm mixing orbit, providing thorough mixing of microplates and/or PCR plates. Up to four plates (standard or deepwell) can be placed on the i ncluded platform and they are instantly secured without the use of any springs, clamps or tools.

A digital microprocessor ensures accurate speed control over the brushless, maintenance free motor drive and both speed and time can be viewed simultaneously on the large LED display.

Ordering Information:

BT1502* Orbi-Shaker MP with platform for 4 microplates

BT1500-A1520 Microtube Adapter (for H6004 only)

For 1.5/2.0mL microtubes

Microtube Adapter (for H6004 only) BT1500-A05

For 0.5mL microtubes *To order an item in 230V, add (-E) to item number.

RBI-SHAKER™ MP

Technical Data: Speed Range: 200 to 1500 rpm Speed Increment 10 rpm 3mm Maximum Capacity: 4 microplates Dimensions (WxDxH): 13.1x11.74x4.7 in. 33x30x12 cm Weight: 12 lbs. / 5.5 kg Operating Temp.: 4 to 65℃ Electrical 100-240V, 50-60 Hz

-Blotter









The Orbi-Blotter features a gentle orbital motion with speed control down to as little as 3 rpm, making it the ideal orbital choice for low speed applications, such as blotting, washing, staining/destaining, etc. A large 14x12 in. platform is included along with a non-slip rubber mat for holding trays, dishes, plates, flasks and other flat bottomed vessels. An optional stacking platform is also available for protocols requiring an increased work surface.

Speed Range:	3 to 70 rpm	BT30*	Orbi-Blotter™ low speed Orbital
Orbit:	19mm (3/4 in.)	The last contract of	
Platform Dims.:	14x12 in./35x30 cm	BR2000-STACK	Stacking Platform, 14 x 12 in. (clea
Dimensions (WxDxH):	14 x 12 x 8 in.	STACK-PLUS	Platform extension set, increase p
	35 x 30 x 20 cm		*To order ar
Weight:	12 lbs. / 5.5 kg		
Operating Temp.:	4°C to 50°C		
Electrical:	120V or 230V, 50-60Hz		OHIO COLORES
		mananana	HILLITON CONTROL OF THE STATE OF

Ordering Information:

BT30*	Orbi-Blotter™ low speed Orbital Shaker with non-slip rubber mat
BR2000-STACK	Stacking Platform, 14 x 12 in. (clearance 2.75 in.)
STACK-PLUS	Platform extension set, increase platrom clearance by 1.25 in.

*To order an item in 230V, add (-E) to item number.

ORBI-SHAKER"

Selection Guide







Model:	Orbi-Shaker JR	Orbi-Shaker	Orbi-Shaker MP	Orbi-Blotter
Max. Speed	300 rpm	300 rpm	1500 rpm	70 rpm
Min. Speed	50 rpm	30 rpm	200 rpm	3 rpm
Orbit Size	19mm	19 mm	3 mm	19 mm
Flask Capacity (125ml)	12	24	N/A	24*
Flask Capacity (250ml)	8	14	N/A	14*
Flask Capacity (500ml)	6	9	N/A	9*
Flask Capacity (1L)	4	5	N/A	5*
Flask Capacity (2L)	N/A	2	N/A	3*
Microplate Capacity	N/A	4	4	N/A
Control	Digital	Digital	Digital	Analog

*For low speed applications (not requiring clamps) only.

Also Available from **Benchmark**





- **+ Exceptional temperature uniformity**
- Extremely compact, just 11" wide
- Exchange flask clamps in one second with the new MAGic Clamp magnetic system





- Designed for use in CO2 Incubators and other extreme environments
- Remote control, adjust settings without exposing chamber
- Exchange flask clamps in one second with MAGic Clamp™ platform.

Benchmark Scientific Inc. PO Box 709 - Edison, NJ 08817 Phone: 908-769-5555 - Fax: 908-222-1864 Web: www.BenchmarkScientific.com Email: Info@BenchmarkScientific.com

